

Q-Band Quadrature Mixer or Phase Detector, 41 to 45 GHz

Description:

Model SFQ-41345311-2222SF-N1 is a Q Band quadrature mixer that covers the frequency range of 41 to 45 GHz. The typical conversion loss of the quadrature mixer is 11 dB with an LO driving power of +16 dBm. The typical LO to RF port isolation is 30 dB. Since the IF port of the quadrature mixer is DC coupled, the mixer can be used as a phase detector. In addition, the mixer can be readily configured into an image rejection mixer or single sideband modulator by adding an IF quadrature coupler.



Features:

- Compact Package
- Low Conversion Loss
- High Port Isolations
- IF Port DC Coupled for Phase Detection

Applications:

- Phase Detection
- Speed and Ranging Radar Systems
- Communication Systems
- Test Equipment

Electrical Specifications:

Parameter	Minimum	Typical	Maximum
RF Frequency	41 GHz		45 GHz
LO Frequency	41 GHz		45 GHz
LO Pumping Power		+16 dBm	+19 dBm
IF Frequency	DC		1.0 GHz
Conversion Loss		11 dB	13 dB
I/Q Phase Unbalance	- / N	±15°	1
I/Q Amplitude Unbalance		±1.0 dB	
LO to RF Port Isolation	20 dB	30 dB	
Combined RF & LO Power			+19 dBm
Specification Temperature	MILLIA	+25 °C	14 A
Operating Temperature	0 °C	CLCI, I	+50 °C

Mechanical Specifications:

Item	Specification
RF Port	WR-22 Waveguide with UG-383/U Flange
LO Port	WR-22 Waveguide with UG-383/U Flange
IF-I Port	SMA(F)
IF-Q Port	SMA(F)
Case Material	Aluminum
Finish	Gold Plated
Weight	3.3 Oz
Size	1.15" (L) 1.15" (W) X 0.88" (H)
Outline	FQ-Q1




www.sagemillimeter.com | 3043 Kashiwa Street, Torrance, CA 90505 Phone: 424-757-0168 | Fax: 424-757-0188 | Email: sales@sagemillimeter.com





Mechanical Outline: (Unless otherwise specified, all dimensions are in inches)



Note:

- The I/Q mixer can be configured as an image rejection mixer or used as an I/Q up-converter, single sideband modulator and phase detector.
- SAGE Millimeter, Inc. reserves the right to change the information presented without notice.

Caution:

- Exceeding absolute maximum ratings will damage the device.
- The mixer is a static sensitive device. Always follow ESD rules when working with the device.
- The IF ports are DC coupled. Use DC blocks if necessary. Do not apply an external bias voltage to the IF port.
- Proper torque, 8.0 ± 0.15 inch-pounds (0.92 \pm 0.05 Nm), should be applied. **SAGE Millimeter** torque wrench, model SCH-08008-S1, is highly recommended.
- Any foreign objects in the waveguide will cause performance degradation and possible device damage.



